

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268380

Luminaire Tested: P3AS20R659735D010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268380  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R659735D010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1091.0 lumens  
Efficiency: N/A  
Efficacy: 37.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268380

CATALOG NUMBER: P3AS20R659735D010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1268380

CATALOG NUMBER: P3AS20R659735D010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 96  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 96  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 90  |
| 3   | 101 | 94  | 88  | 84  | 99  | 92  | 87  | 83  | 90  | 85  | 82  |  | 87  | 84  | 81  |  | 85  |
| 4   | 95  | 87  | 81  | 76  | 93  | 86  | 80  | 76  | 84  | 79  | 75  |  | 82  | 78  | 74  |  | 80  |
| 5   | 90  | 81  | 75  | 70  | 88  | 80  | 74  | 70  | 78  | 73  | 69  |  | 77  | 72  | 69  |  | 75  |
| 6   | 85  | 76  | 69  | 65  | 84  | 75  | 69  | 65  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 55  |  | 63  |
| 9   | 73  | 63  | 57  | 52  | 72  | 62  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 59  |
| 10  | 69  | 59  | 53  | 49  | 68  | 59  | 53  | 49  | 58  | 53  | 49  |  | 57  | 52  | 49  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 277324 |
| 5°  | 270415 |
| 10° | 251832 |
| 15° | 225677 |
| 20° | 194897 |
| 25° | 162130 |
| 30° | 127842 |
| 35° | 94736  |
| 40° | 65294  |
| 45° | 40500  |
| 50° | 22004  |
| 55° | 13839  |
| 60° | 11710  |
| 65° | 10585  |
| 70° | 9104   |
| 75° | 7964   |
| 80° | 7956   |
| 85° | 7799   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40500 cd/sqm

TEST NUMBER: P1268380

CATALOG NUMBER: P3AS20R659735D010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 114.2  | 10.5      |
| 10°-20°   | 276.3  | 25.3      |
| 20°-30°   | 305.5  | 28.0      |
| 30°-40°   | 221.9  | 20.3      |
| 40°-50°   | 104.0  | 9.5       |
| 50°-60°   | 35.0   | 3.2       |
| 60°-70°   | 20.2   | 1.9       |
| 70°-80°   | 10.6   | 1.0       |
| 80°-90°   | 3.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 695.9  | 63.8      |
| 0°-40°    | 917.8  | 84.1      |
| 0°-60°    | 1056.8 | 96.9      |
| 0°-90°    | 1091.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1091.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1265 |      |
| 5°  | 1228 | 114  |
| 15° | 994  | 276  |
| 25° | 670  | 306  |
| 35° | 354  | 222  |
| 45° | 131  | 104  |
| 55° | 36   | 35   |
| 65° | 20   | 20   |
| 75° | 9    | 11   |
| 85° | 3    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1268380

CATALOG NUMBER: P3AS20R659735D010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1264.7 |
| 2.5°  | 1256.8 |
| 5°    | 1228.5 |
| 7.5°  | 1186.0 |
| 10°   | 1131.0 |
| 12.5° | 1066.5 |
| 15°   | 994.1  |
| 17.5° | 915.5  |
| 20°   | 835.2  |
| 22.5° | 751.9  |
| 25°   | 670.1  |
| 27.5° | 586.7  |
| 30°   | 504.9  |
| 32.5° | 426.3  |
| 35°   | 353.9  |
| 37.5° | 287.9  |
| 40°   | 228.1  |
| 42.5° | 174.6  |
| 45°   | 130.6  |
| 47.5° | 94.4   |
| 50°   | 64.5   |
| 52.5° | 44.0   |
| 55°   | 36.2   |
| 57.5° | 31.5   |
| 60°   | 26.7   |
| 62.5° | 23.6   |
| 65°   | 20.4   |
| 67.5° | 17.3   |
| 70°   | 14.2   |
| 72.5° | 12.6   |
| 75°   | 9.4    |
| 77.5° | 7.9    |
| 80°   | 6.3    |
| 82.5° | 4.7    |
| 85°   | 3.1    |
| 87.5° | 1.6    |
| 90°   | 0.0    |

(END OF REPORT)