

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267509

Luminaire Tested: P3AS13R409735DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409735DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 809.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267509
CATALOG NUMBER: P3AS13R409735DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1267509
 CATALOG NUMBER: P3AS13R409735DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181608
5°	178318
10°	168089
15°	152668
20°	134108
25°	114539
30°	94875
35°	73160
40°	52069
45°	35073
50°	19138
55°	13495
60°	12718
65°	11726
70°	10450
75°	9997
80°	7956
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 35073 cd/sqm



TEST NUMBER: P1267509
 CATALOG NUMBER: P3AS13R409735DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	9.3
10°-20°	187.3	23.2
20°-30°	216.6	26.8
30°-40°	170.7	21.1
40°-50°	87.6	10.8
50°-60°	33.5	4.1
60°-70°	22.1	2.7
70°-80°	12.1	1.5
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.4	59.3
0°-40°	650.1	80.4
0°-60°	771.2	95.3
0°-90°	809.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	809.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	828	
5°	810	76
15°	672	187
25°	473	217
35°	273	171
45°	113	88
55°	35	33
65°	23	22
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P1267509
CATALOG NUMBER: P3AS13R409735DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	828.2
2.5°	823.7
5°	810.1
7.5°	786.5
10°	754.9
12.5°	717.8
15°	672.5
17.5°	625.4
20°	574.7
22.5°	523.2
25°	473.4
27.5°	423.6
30°	374.7
32.5°	324.9
35°	273.3
37.5°	225.4
40°	181.9
42.5°	144.8
45°	113.1
47.5°	82.4
50°	56.1
52.5°	40.7
55°	35.3
57.5°	31.7
60°	29.0
62.5°	25.3
65°	22.6
67.5°	19.0
70°	16.3
72.5°	13.6
75°	11.8
77.5°	9.1
80°	6.3
82.5°	5.4
85°	2.7
87.5°	1.8
90°	0.0

(END OF REPORT)