

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267536

Luminaire Tested: P3AS13R459735DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459735DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 320.0 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267536

CATALOG NUMBER: P3AS13R459735DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267536

CATALOG NUMBER: P3AS13R459735DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95321
5°	93132
10°	85926
15°	74711
20°	61372
25°	47761
30°	35271
35°	24815
40°	15486
45°	8404
50°	4537
55°	3900
60°	3508
65°	3009
70°	2565
75°	2626
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8404 cd/sqm

TEST NUMBER: P1267536

CATALOG NUMBER: P3AS13R459735DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	12.2
10°-20°	91.0	28.4
20°-30°	90.3	28.2
30°-40°	58.2	18.2
40°-50°	22.4	7.0
50°-60°	9.1	2.8
60°-70°	5.8	1.8
70°-80°	3.1	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.5	68.9
0°-40°	278.7	87.1
0°-60°	310.2	96.9
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	435	
5°	423	39
15°	329	91
25°	197	90
35°	93	58
45°	27	22
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1267536

CATALOG NUMBER: P3AS13R459735DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	434.7
2.5°	432.5
5°	423.1
7.5°	407.2
10°	385.9
12.5°	359.3
15°	329.1
17.5°	296.3
20°	263.0
22.5°	229.3
25°	197.4
27.5°	167.2
30°	139.3
32.5°	114.9
35°	92.7
37.5°	72.7
40°	54.1
42.5°	39.0
45°	27.1
47.5°	18.2
50°	13.3
52.5°	11.1
55°	10.2
57.5°	8.9
60°	8.0
62.5°	6.7
65°	5.8
67.5°	4.9
70°	4.0
72.5°	3.5
75°	3.1
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)