

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268384

Luminaire Tested: P3AS20R709735D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709735D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1970.0 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268384
CATALOG NUMBER: P3AS20R709735D010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1268384
 CATALOG NUMBER: P3AS20R709735D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391197
5°	373277
10°	355148
15°	345655
20°	332879
25°	315067
30°	293032
35°	246143
40°	158640
45°	73744
50°	19343
55°	4817
60°	4824
65°	4099
70°	4039
75°	3982
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 73744 cd/sqm



TEST NUMBER: P1268384
 CATALOG NUMBER: P3AS20R709735D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	8.1
10°-20°	427.8	21.7
20°-30°	597.8	30.3
30°-40°	554.2	28.1
40°-50°	198.7	10.1
50°-60°	16.8	0.9
60°-70°	8.4	0.4
70°-80°	5.4	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1184.3	60.1
0°-40°	1738.5	88.3
0°-60°	1954.1	99.2
0°-90°	1970.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1970.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1784	
5°	1696	159
15°	1523	428
25°	1302	598
35°	920	554
45°	238	199
55°	13	17
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1268384
CATALOG NUMBER: P3AS20R709735D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1784.0
2.5°	1757.2
5°	1695.8
7.5°	1639.1
10°	1595.0
12.5°	1558.8
15°	1522.6
17.5°	1478.5
20°	1426.5
22.5°	1366.7
25°	1302.2
27.5°	1236.0
30°	1157.3
32.5°	1056.5
35°	919.5
37.5°	744.8
40°	554.2
42.5°	377.9
45°	237.8
47.5°	132.3
50°	56.7
52.5°	18.9
55°	12.6
57.5°	11.0
60°	11.0
62.5°	9.4
65°	7.9
67.5°	7.9
70°	6.3
72.5°	6.3
75°	4.7
77.5°	4.7
80°	3.1
82.5°	3.1
85°	1.6
87.5°	1.6
90°	0.0

(END OF REPORT)