

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267553

Luminaire Tested: P3AS13R509735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 499.0 lumens
Efficiency: N/A
Efficacy: 34.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267553

CATALOG NUMBER: P3AS13R509735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267553

CATALOG NUMBER: P3AS13R509735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158869
5°	155668
10°	145822
15°	130534
20°	109840
25°	83835
30°	54489
35°	32310
40°	18664
45°	9365
50°	3480
55°	2714
60°	2544
65°	2283
70°	2244
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9365 cd/sqm

TEST NUMBER: P1267553

CATALOG NUMBER: P3AS13R509735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.8	13.2
10°-20°	159.0	31.9
20°-30°	156.0	31.3
30°-40°	78.6	15.8
40°-50°	24.8	5.0
50°-60°	6.4	1.3
60°-70°	4.5	0.9
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.8	76.3
0°-40°	459.4	92.1
0°-60°	490.7	98.3
0°-90°	499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	499.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	724	
5°	707	66
15°	575	159
25°	346	156
35°	121	79
45°	30	25
55°	7	6
65°	4	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1267553

CATALOG NUMBER: P3AS13R509735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	724.5
2.5°	720.1
5°	707.2
7.5°	684.1
10°	654.9
12.5°	617.1
15°	575.0
17.5°	526.2
20°	470.7
22.5°	410.8
25°	346.5
27.5°	278.2
30°	215.2
32.5°	161.9
35°	120.7
37.5°	89.2
40°	65.2
42.5°	46.1
45°	30.2
47.5°	17.3
50°	10.2
52.5°	7.5
55°	7.1
57.5°	6.2
60°	5.8
62.5°	5.3
65°	4.4
67.5°	4.0
70°	3.5
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)