

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268482

Luminaire Tested: P3AS02R109740DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1268482  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R109740DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 97CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 169.0 lumens  
Efficiency: N/A  
Efficacy: 44.5 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268482  
CATALOG NUMBER: P3AS02R109740DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1268482  
 CATALOG NUMBER: P3AS02R109740DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	83	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72	72	72	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	70	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55	55	55	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	49185
5°	46093
10°	37808
15°	29376
20°	23172
25°	18485
30°	14838
35°	12100
40°	9962
45°	8404
50°	7198
55°	6232
60°	5526
65°	4825
70°	4296
75°	3474
80°	2778
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8404 cd/sqm



TEST NUMBER: P1268482

CATALOG NUMBER: P3AS02R109740DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.7	11.1
10°-20°	36.2	21.4
20°-30°	35.2	20.8
30°-40°	28.5	16.8
40°-50°	21.1	12.5
50°-60°	14.8	8.7
60°-70°	9.3	5.5
70°-80°	4.4	2.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.2	53.3
0°-40°	118.6	70.2
0°-60°	154.5	91.4
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	224	
5°	209	19
15°	129	36
25°	76	35
35°	45	28
45°	27	21
55°	16	15
65°	9	9
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1268482  
CATALOG NUMBER: P3AS02R109740DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	224.3
2.5°	220.6
5°	209.4
7.5°	191.7
10°	169.8
12.5°	148.3
15°	129.4
17.5°	113.4
20°	99.3
22.5°	87.1
25°	76.4
27.5°	66.7
30°	58.6
32.5°	51.5
35°	45.2
37.5°	39.7
40°	34.8
42.5°	30.8
45°	27.1
47.5°	24.1
50°	21.1
52.5°	18.5
55°	16.3
57.5°	14.5
60°	12.6
62.5°	10.8
65°	9.3
67.5°	7.8
70°	6.7
72.5°	5.2
75°	4.1
77.5°	3.0
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)