

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268540

Luminaire Tested: P3AS02R159740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 71.0 lumens
Efficiency: N/A
Efficacy: 19.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268540

CATALOG NUMBER: P3AS02R159740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268540

CATALOG NUMBER: P3AS02R159740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	99	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30612
5°	28307
10°	22600
15°	17072
20°	12998
25°	9896
30°	7090
35°	4631
40°	2834
45°	1706
50°	1126
55°	879
60°	746
65°	675
70°	577
75°	593
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1706 cd/sqm

TEST NUMBER: P1268540

CATALOG NUMBER: P3AS02R159740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.4	16.0
10°-20°	21.0	29.6
20°-30°	18.7	26.3
30°-40°	11.1	15.6
40°-50°	4.5	6.4
50°-60°	2.1	3.0
60°-70°	1.3	1.8
70°-80°	0.7	1.0
80°-90°	0.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	51.1	72.0
0°-40°	62.2	87.6
0°-60°	68.9	97.0
0°-90°	71.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	71.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	140	
5°	129	11
15°	75	21
25°	41	19
35°	17	11
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268540

CATALOG NUMBER: P3AS02R159740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	139.6
1°	139.3
2°	138.2
3°	136.2
4°	132.7
5°	128.6
6°	124.1
7°	118.8
8°	113.2
9°	107.6
10°	101.5
12.5°	87.5
15°	75.2
17.5°	64.6
20°	55.7
22.5°	47.8
25°	40.9
27.5°	34.2
30°	28.0
32.5°	22.4
35°	17.3
37.5°	13.3
40°	9.9
42.5°	7.4
45°	5.5
47.5°	4.3
50°	3.3
52.5°	2.8
55°	2.3
57.5°	2.0
60°	1.7
62.5°	1.5
65°	1.3
67.5°	1.2
70°	0.9
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)