

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268558

Luminaire Tested: P3AS02R209740DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1268558  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209740DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 296.0 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1268558  
CATALOG NUMBER: P3AS02R209740DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1268558  
 CATALOG NUMBER: P3AS02R209740DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 99 | 100 |
| 1   | 115 | 114 | 112 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 100 | 99  | 97  | 97  | 96 | 97  |
| 2   | 112 | 109 | 106 | 104 | 110 | 107 | 105 | 103 | 104 | 102 | 101 | 101 | 100 | 98  | 99  | 98  | 96  | 95  | 95  | 94 | 95  |
| 3   | 109 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 99  | 97  | 99  | 97  | 95  | 97  | 95  | 94  | 93  | 93  | 92 | 93  |
| 4   | 106 | 101 | 98  | 95  | 105 | 100 | 97  | 95  | 99  | 96  | 94  | 97  | 95  | 93  | 95  | 93  | 92  | 91  | 91  | 90 | 91  |
| 5   | 104 | 98  | 95  | 92  | 102 | 98  | 94  | 92  | 96  | 93  | 91  | 95  | 92  | 90  | 93  | 91  | 90  | 89  | 89  | 88 | 89  |
| 6   | 101 | 96  | 92  | 89  | 100 | 95  | 92  | 89  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 89  | 88  | 87  | 87  | 86 | 87  |
| 7   | 99  | 93  | 90  | 87  | 98  | 93  | 89  | 87  | 92  | 89  | 86  | 91  | 88  | 86  | 90  | 87  | 86  | 85  | 85  | 84 | 85  |
| 8   | 97  | 91  | 87  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 88  | 86  | 84  | 83  | 83  | 82 | 83  |
| 9   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 83  | 88  | 85  | 83  | 87  | 84  | 83  | 87  | 84  | 82  | 81  | 81  | 80 | 81  |
| 10  | 93  | 87  | 84  | 81  | 92  | 87  | 83  | 81  | 86  | 83  | 81  | 86  | 83  | 81  | 85  | 83  | 81  | 80  | 80  | 79 | 80  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 448999 |
| 5°  | 378053 |
| 10° | 236112 |
| 15° | 88287  |
| 20° | 30313  |
| 25° | 12630  |
| 30° | 5950   |
| 35° | 2677   |
| 40° | 1260   |
| 45° | 651    |
| 50° | 239    |
| 55° | 38     |
| 60° | 44     |
| 65° | 52     |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 651 cd/sqm



TEST NUMBER: P1268558  
 CATALOG NUMBER: P3AS02R209740DE010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 142.8  | 48.3      |
| 10°-20°   | 117.6  | 39.7      |
| 20°-30°   | 26.7   | 9.0       |
| 30°-40°   | 6.8    | 2.3       |
| 40°-50°   | 1.7    | 0.6       |
| 50°-60°   | 0.2    | 0.1       |
| 60°-70°   | 0.1    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 287.2  | 97.0      |
| 0°-40°    | 294.0  | 99.3      |
| 0°-60°    | 295.9  | 100.0     |
| 0°-90°    | 296.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 296.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2048 |      |
| 5°  | 1718 | 143  |
| 15° | 389  | 118  |
| 25° | 52   | 27   |
| 35° | 10   | 7    |
| 45° | 2    | 2    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1268558  
CATALOG NUMBER: P3AS02R209740DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2047.6 |
| 1°    | 2030.3 |
| 2°    | 1979.1 |
| 3°    | 1905.8 |
| 4°    | 1815.7 |
| 5°    | 1717.5 |
| 6°    | 1608.0 |
| 7°    | 1487.2 |
| 8°    | 1346.2 |
| 9°    | 1206.5 |
| 10°   | 1060.4 |
| 11°   | 905.0  |
| 12°   | 749.8  |
| 13°   | 618.4  |
| 14°   | 492.7  |
| 15°   | 388.9  |
| 16°   | 306.9  |
| 17°   | 242.1  |
| 18°   | 194.5  |
| 19°   | 158.2  |
| 20°   | 129.9  |
| 21°   | 108.6  |
| 22°   | 90.6   |
| 23°   | 75.3   |
| 24°   | 62.8   |
| 25°   | 52.2   |
| 27.5° | 34.1   |
| 30°   | 23.5   |
| 32.5° | 14.5   |
| 35°   | 10.0   |
| 37.5° | 6.4    |
| 40°   | 4.4    |
| 42.5° | 3.0    |
| 45°   | 2.1    |
| 47.5° | 1.4    |
| 50°   | 0.7    |
| 52.5° | 0.3    |
| 55°   | 0.1    |
| 57.5° | 0.1    |
| 60°   | 0.1    |
| 62.5° | 0.1    |
| 65°   | 0.1    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |



TEST NUMBER: P1268558  
CATALOG NUMBER: P3AS02R209740DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)