

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267570

Luminaire Tested: P3AS13R509735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 669.0 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267570

CATALOG NUMBER: P3AS13R509735DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1267570

CATALOG NUMBER: P3AS13R509735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194568
5°	189346
10°	174590
15°	153554
20°	128461
25°	101861
30°	74746
35°	51397
40°	32661
45°	18265
50°	9893
55°	8296
60°	7149
65°	6590
70°	5834
75°	5338
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18265 cd/sqm

TEST NUMBER: P1267570

CATALOG NUMBER: P3AS13R509735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	11.9
10°-20°	187.3	28.0
20°-30°	191.6	28.6
30°-40°	121.5	18.2
40°-50°	48.3	7.2
50°-60°	19.6	2.9
60°-70°	12.6	1.9
70°-80°	6.4	1.0
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.6	68.6
0°-40°	580.1	86.7
0°-60°	648.0	96.9
0°-90°	669.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	887	
5°	860	80
15°	676	187
25°	421	192
35°	192	121
45°	59	48
55°	22	20
65°	13	13
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1267570

CATALOG NUMBER: P3AS13R509735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	887.3
2.5°	881.0
5°	860.2
7.5°	827.6
10°	784.1
12.5°	732.5
15°	676.4
17.5°	614.8
20°	550.5
22.5°	486.2
25°	421.0
27.5°	355.8
30°	295.2
32.5°	240.8
35°	192.0
37.5°	150.3
40°	114.1
42.5°	84.2
45°	58.9
47.5°	39.8
50°	29.0
52.5°	24.4
55°	21.7
57.5°	19.0
60°	16.3
62.5°	14.5
65°	12.7
67.5°	10.9
70°	9.1
72.5°	7.2
75°	6.3
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)