

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267607

Luminaire Tested: P3AS13R609735DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609735DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1084.9 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267607
CATALOG NUMBER: P3AS13R609735DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1267607

CATALOG NUMBER: P3AS13R609735DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284275
5°	268368
10°	261385
15°	255416
20°	237484
25°	212311
30°	162177
35°	93612
40°	36325
45°	15133
50°	3343
55°	497
60°	395
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15133 cd/sqm



TEST NUMBER: P1267607

CATALOG NUMBER: P3AS13R609735DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.1	10.6
10°-20°	313.4	28.9
20°-30°	392.5	36.2
30°-40°	219.4	20.2
40°-50°	41.7	3.8
50°-60°	2.1	0.2
60°-70°	0.5	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	821.0	75.7
0°-40°	1040.5	95.9
0°-60°	1084.3	99.9
0°-90°	1084.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1084.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1296	
5°	1219	115
15°	1125	313
25°	878	393
35°	350	219
45°	49	42
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1267607

CATALOG NUMBER: P3AS13R609735DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1296.4
1°	1291.1
2°	1274.3
3°	1254.3
4°	1235.6
5°	1219.2
6°	1206.8
7°	1196.1
8°	1188.1
9°	1180.6
10°	1173.9
11°	1167.3
12°	1159.7
13°	1150.4
14°	1139.3
15°	1125.1
16°	1107.8
17°	1088.3
18°	1066.1
19°	1040.8
20°	1017.7
21°	992.9
22°	967.1
23°	940.0
24°	910.3
25°	877.5
26°	838.8
27°	795.8
28°	747.4
29°	695.9
30°	640.5
31°	584.5
32°	526.8
32.5°	495.3
33°	466.9
34°	407.9
35°	349.7
36°	297.4
37°	241.9
37.5°	216.6
38°	191.7
39°	154.5
40°	126.9
42.5°	77.2
45°	48.8



TEST NUMBER: P1267607
CATALOG NUMBER: P3AS13R609735DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	27.1
50°	9.8
52.5°	2.2
55°	1.3
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)