

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267608

Luminaire Tested: P3AS13R609735DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R609735DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1171.0 lumens  
Efficiency: N/A  
Efficacy: 80.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267608  
CATALOG NUMBER: P3AS13R609735DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1267608  
 CATALOG NUMBER: P3AS13R609735DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71				71
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	70	68	66				66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	63	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	279627
5°	268544
10°	276481
15°	280024
20°	247285
25°	208391
30°	169013
35°	110075
40°	50552
45°	19382
50°	6482
55°	1720
60°	1579
65°	1401
70°	1154
75°	1525
80°	1137
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19382 cd/sqm



TEST NUMBER: P1267608  
 CATALOG NUMBER: P3AS13R609735DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	117.4	10.0
10°-20°	337.8	28.8
20°-30°	394.0	33.6
30°-40°	254.3	21.7
40°-50°	57.0	4.9
50°-60°	5.7	0.5
60°-70°	2.7	0.2
70°-80°	1.5	0.1
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	849.2	72.5
0°-40°	1103.5	94.2
0°-60°	1166.1	99.6
0°-90°	1171.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1171.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1275	
5°	1220	117
15°	1234	338
25°	861	394
35°	411	254
45°	62	57
55°	4	6
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1267608  
CATALOG NUMBER: P3AS13R609735DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1275.2
2.5°	1254.4
5°	1220.0
7.5°	1218.1
10°	1241.7
12.5°	1257.1
15°	1233.5
17.5°	1162.9
20°	1059.7
22.5°	951.9
25°	861.3
27.5°	772.6
30°	667.5
32.5°	544.3
35°	411.2
37.5°	280.8
40°	176.6
42.5°	106.0
45°	62.5
47.5°	36.2
50°	19.0
52.5°	6.3
55°	4.5
57.5°	3.6
60°	3.6
62.5°	2.7
65°	2.7
67.5°	2.7
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)