

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268586

Luminaire Tested: P3AS02R259740DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259740DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 121.0 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268586
CATALOG NUMBER: P3AS02R259740DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1268586

CATALOG NUMBER: P3AS02R259740DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	82	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77625
5°	72419
10°	58004
15°	39387
20°	23825
25°	13936
30°	7925
35°	4363
40°	2319
45°	1209
50°	716
55°	535
60°	439
65°	467
70°	449
75°	424
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1209 cd/sqm



TEST NUMBER: P1268586
 CATALOG NUMBER: P3AS02R259740DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	24.1
10°-20°	47.7	39.4
20°-30°	27.3	22.5
30°-40°	10.8	8.9
40°-50°	3.3	2.7
50°-60°	1.3	1.1
60°-70°	0.9	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.1	86.1
0°-40°	114.9	95.0
0°-60°	119.5	98.8
0°-90°	121.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	121.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	354	
5°	329	29
15°	174	48
25°	58	27
35°	16	11
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1268586
CATALOG NUMBER: P3AS02R259740DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	354.0
1°	353.3
2°	350.4
3°	345.3
4°	338.2
5°	329.0
6°	318.1
7°	305.9
8°	291.6
9°	277.1
10°	260.5
11°	244.2
12°	226.3
13°	208.6
14°	190.5
15°	173.5
17.5°	134.5
20°	102.1
22.5°	76.7
25°	57.6
27.5°	42.7
30°	31.3
32.5°	22.7
35°	16.3
37.5°	11.6
40°	8.1
42.5°	5.6
45°	3.9
47.5°	2.8
50°	2.1
52.5°	1.6
55°	1.4
57.5°	1.3
60°	1.0
62.5°	0.9
65°	0.9
67.5°	0.8
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1268586
CATALOG NUMBER: P3AS02R259740DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)