

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267639

Luminaire Tested: P3AS13R659735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1080.0 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267639

CATALOG NUMBER: P3AS13R659735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267639

CATALOG NUMBER: P3AS13R659735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	95	91	88	93	89	86		90	87	85		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	65	83	75	69	65	73	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		68
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289385
5°	268698
10°	259848
15°	250421
20°	231510
25°	210932
30°	162987
35°	94469
40°	37499
45°	15971
50°	3787
55°	497
60°	395
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15971 cd/sqm

TEST NUMBER: P1267639

CATALOG NUMBER: P3AS13R659735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.1	10.7
10°-20°	307.4	28.5
20°-30°	389.0	36.0
30°-40°	221.5	20.5
40°-50°	44.0	4.1
50°-60°	2.3	0.2
60°-70°	0.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	811.5	75.1
0°-40°	1033.1	95.7
0°-60°	1079.3	99.9
0°-90°	1080.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1080.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1320	
5°	1221	115
15°	1103	307
25°	872	389
35°	353	222
45°	52	44
55°	1	2
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267639

CATALOG NUMBER: P3AS13R659735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1319.7
1°	1310.0
2°	1288.7
3°	1263.8
4°	1239.4
5°	1220.7
6°	1207.0
7°	1195.9
8°	1186.1
9°	1176.4
10°	1167.0
11°	1156.8
12°	1146.2
13°	1133.3
14°	1119.5
15°	1103.1
16°	1083.6
17°	1062.3
18°	1039.2
19°	1014.8
20°	992.1
21°	969.1
22°	948.2
23°	926.4
24°	901.1
25°	871.8
26°	836.8
27°	794.6
28°	747.1
29°	696.5
30°	643.7
31°	585.5
32°	527.8
32.5°	498.1
33°	469.2
34°	410.6
35°	352.9
36°	299.6
37°	246.8
37.5°	219.7
38°	198.0
39°	160.3
40°	131.0
42.5°	80.8
45°	51.5



TEST NUMBER: P1267639

CATALOG NUMBER: P3AS13R659735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	30.2
50°	11.1
52.5°	2.2
55°	1.3
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)