

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268617

Luminaire Tested: P3AS02R309740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 298.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268617

CATALOG NUMBER: P3AS02R309740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268617

CATALOG NUMBER: P3AS02R309740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	100	97	106	102	99	96	99	97	95		97	95	93		95
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93
5	101	96	92	89	100	95	91	88	93	90	87		92	89	87		90
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		82
10	88	82	78	75	88	81	78	75	81	77	75		80	77	75		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237108
5°	234008
10°	204316
15°	129853
20°	51454
25°	17178
30°	8001
35°	3614
40°	1403
45°	682
50°	205
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 682 cd/sqm

TEST NUMBER: P1268617

CATALOG NUMBER: P3AS02R309740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	32.6
10°-20°	150.7	50.6
20°-30°	38.9	13.0
30°-40°	9.1	3.1
40°-50°	1.8	0.6
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.8	96.2
0°-40°	295.9	99.3
0°-60°	297.9	100.0
0°-90°	298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1081	
5°	1063	97
15°	572	151
25°	71	39
35°	14	9
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268617

CATALOG NUMBER: P3AS02R309740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1081.3
1°	1080.4
2°	1077.9
3°	1075.0
4°	1070.7
5°	1063.1
6°	1050.7
7°	1030.1
8°	1002.0
9°	965.3
10°	917.6
11°	860.8
12°	798.8
13°	727.4
14°	652.7
15°	572.0
16°	493.0
17°	416.9
18°	343.9
19°	276.9
20°	220.5
21°	173.5
22°	136.5
23°	108.0
24°	86.5
25°	71.0
26°	59.2
27°	50.3
28°	43.5
29°	37.2
30°	31.6
32.5°	19.9
35°	13.5
37.5°	8.4
40°	4.9
42.5°	3.2
45°	2.2
47.5°	1.3
50°	0.6
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1



TEST NUMBER: P1268617

CATALOG NUMBER: P3AS02R309740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)