

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268619

Luminaire Tested: P3AS02R309740DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309740DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 250.0 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268619

CATALOG NUMBER: P3AS02R309740DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1268619

CATALOG NUMBER: P3AS02R309740DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	85	81	77		84	80	77		83	79	76		81	78	76
7	90	82	77	74		89	82	77	74		81	76	73		80	76	73		78	75	73
8	87	79	74	71		86	79	74	71		78	73	70		77	73	70		76	72	70
9	84	76	71	68		83	75	71	68		75	70	67		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	67	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145887
5°	138851
10°	116787
15°	84223
20°	52248
25°	29711
30°	16509
35°	8968
40°	4723
45°	2574
50°	1365
55°	918
60°	833
65°	882
70°	769
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2574 cd/sqm

TEST NUMBER: P1268619

CATALOG NUMBER: P3AS02R309740DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	22.7
10°-20°	101.0	40.4
20°-30°	58.4	23.3
30°-40°	22.1	8.9
40°-50°	6.8	2.7
50°-60°	2.3	0.9
60°-70°	1.6	0.6
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	216.1	86.4
0°-40°	238.3	95.3
0°-60°	247.4	98.9
0°-90°	250.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	250.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	665	
5°	631	57
15°	371	101
25°	123	58
35°	34	22
45°	8	7
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268619

CATALOG NUMBER: P3AS02R309740DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	665.3
1°	664.8
2°	660.8
3°	653.2
4°	643.8
5°	630.8
6°	614.3
7°	595.8
8°	575.3
9°	550.7
10°	524.5
11°	496.2
12°	466.2
13°	434.8
14°	402.9
15°	371.0
17.5°	292.6
20°	223.9
22.5°	166.0
25°	122.8
27.5°	89.3
30°	65.2
32.5°	47.0
35°	33.5
37.5°	23.4
40°	16.5
42.5°	11.6
45°	8.3
47.5°	5.7
50°	4.0
52.5°	2.8
55°	2.4
57.5°	2.1
60°	1.9
62.5°	1.7
65°	1.7
67.5°	1.4
70°	1.2
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1268619

CATALOG NUMBER: P3AS02R309740DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)