

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267679

Luminaire Tested: P3AS13R709735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 912.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267679

CATALOG NUMBER: P3AS13R709735DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1267679

CATALOG NUMBER: P3AS13R709735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176565
5°	174444
10°	169402
15°	162226
20°	151960
25°	138056
30°	119259
35°	95031
40°	69215
45°	45493
50°	21321
55°	6576
60°	6359
65°	6123
70°	5834
75°	6100
80°	5683
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45493 cd/sqm

TEST NUMBER: P1267679

CATALOG NUMBER: P3AS13R709735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	8.2
10°-20°	200.0	21.9
20°-30°	259.9	28.5
30°-40°	220.6	24.2
40°-50°	113.7	12.5
50°-60°	21.9	2.4
60°-70°	11.9	1.3
70°-80°	7.3	0.8
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.6	58.6
0°-40°	755.1	82.8
0°-60°	890.8	97.7
0°-90°	912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	805	
5°	792	75
15°	715	200
25°	571	260
35°	355	221
45°	147	114
55°	17	22
65°	12	12
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1267679

CATALOG NUMBER: P3AS13R709735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	805.2
2.5°	802.4
5°	792.5
7.5°	778.0
10°	760.8
12.5°	739.0
15°	714.6
17.5°	684.7
20°	651.2
22.5°	613.2
25°	570.6
27.5°	522.6
30°	471.0
32.5°	413.9
35°	355.0
37.5°	297.1
40°	241.8
42.5°	190.2
45°	146.7
47.5°	107.8
50°	62.5
52.5°	27.2
55°	17.2
57.5°	16.3
60°	14.5
62.5°	13.6
65°	11.8
67.5°	10.9
70°	9.1
72.5°	8.2
75°	7.2
77.5°	5.4
80°	4.5
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)