

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268637

Luminaire Tested: P3AS02R309740DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309740DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 184.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268637

CATALOG NUMBER: P3AS02R309740DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1268637

CATALOG NUMBER: P3AS02R309740DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45347
5°	43341
10°	37385
15°	30988
20°	25389
25°	20469
30°	16509
35°	13518
40°	11221
45°	9520
50°	8153
55°	7034
60°	6271
65°	5500
70°	4809
75°	4067
80°	3031
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9520 cd/sqm

TEST NUMBER: P1268637

CATALOG NUMBER: P3AS02R309740DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.8	9.7
10°-20°	38.1	20.7
20°-30°	39.0	21.2
30°-40°	31.9	17.3
40°-50°	23.9	13.0
50°-60°	16.8	9.1
60°-70°	10.6	5.7
70°-80°	5.1	2.8
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.9	51.6
0°-40°	126.8	68.9
0°-60°	167.4	91.0
0°-90°	184.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	184.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	207	
5°	197	18
15°	136	38
25°	85	39
35°	50	32
45°	31	24
55°	18	17
65°	11	11
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1268637

CATALOG NUMBER: P3AS02R309740DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	206.8
2.5°	204.7
5°	196.9
7.5°	183.9
10°	167.9
12.5°	152.2
15°	136.5
17.5°	122.2
20°	108.8
22.5°	96.2
25°	84.6
27.5°	74.4
30°	65.2
32.5°	57.7
35°	50.5
37.5°	44.7
40°	39.2
42.5°	34.8
45°	30.7
47.5°	27.0
50°	23.9
52.5°	21.2
55°	18.4
57.5°	16.4
60°	14.3
62.5°	12.3
65°	10.6
67.5°	8.9
70°	7.5
72.5°	6.1
75°	4.8
77.5°	3.4
80°	2.4
82.5°	1.4
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)