

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268677

Luminaire Tested: P3AS02R409740DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409740DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268677

CATALOG NUMBER: P3AS02R409740DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1268677

CATALOG NUMBER: P3AS02R409740DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	78		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	168210
5°	167004
10°	162633
15°	145268
20°	96328
25°	36075
30°	9647
35°	3774
40°	1345
45°	651
50°	205
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 651 cd/sqm

TEST NUMBER: P1268677

CATALOG NUMBER: P3AS02R409740DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	21.7
10°-20°	169.6	51.4
20°-30°	76.9	23.3
30°-40°	10.0	3.0
40°-50°	1.7	0.5
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	318.0	96.4
0°-40°	328.0	99.4
0°-60°	329.9	100.0
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	767	
5°	759	72
15°	640	170
25°	149	77
35°	14	10
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268677

CATALOG NUMBER: P3AS02R409740DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	767.1
1°	766.6
2°	765.5
3°	763.7
4°	761.5
5°	758.7
6°	755.3
7°	751.1
8°	746.1
9°	739.1
10°	730.4
11°	720.1
12°	706.3
13°	689.3
14°	667.2
15°	639.9
16°	605.1
17°	565.5
18°	517.9
19°	467.6
20°	412.8
21°	357.9
22°	303.8
23°	250.0
24°	197.1
25°	149.1
26°	110.4
27°	80.9
28°	60.8
29°	47.3
30°	38.1
31°	31.5
32°	26.3
32.5°	24.0
33°	21.7
34°	17.7
35°	14.1
36°	11.1
37°	8.8
37.5°	7.9
38°	6.9
39°	5.8
40°	4.7
42.5°	3.1
45°	2.1



TEST NUMBER: P1268677

CATALOG NUMBER: P3AS02R409740DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.3
50°	0.6
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)