

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267705

Luminaire Tested: P3AS17R159735DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267705
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159735DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 947.0 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267705

CATALOG NUMBER: P3AS17R159735DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267705

CATALOG NUMBER: P3AS17R159735DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238862
5°	232379
10°	212376
15°	186017
20°	159567
25°	133242
30°	106624
35°	79960
40°	58023
45°	37957
50°	23743
55°	16057
60°	14209
65°	13075
70°	12310
75°	11184
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37957 cd/sqm

TEST NUMBER: P1267705

CATALOG NUMBER: P3AS17R159735DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.4	10.3
10°-20°	228.3	24.1
20°-30°	251.6	26.6
30°-40°	188.4	19.9
40°-50°	97.7	10.3
50°-60°	40.5	4.3
60°-70°	25.1	2.6
70°-80°	14.1	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.3	61.0
0°-40°	765.6	80.8
0°-60°	903.8	95.4
0°-90°	947.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	947.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1089	
5°	1056	97
15°	819	228
25°	551	252
35°	299	188
45°	122	98
55°	42	40
65°	25	25
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P1267705

CATALOG NUMBER: P3AS17R159735DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1089.3
1°	1090.5
2°	1086.9
3°	1079.7
4°	1068.9
5°	1055.7
6°	1038.9
7°	1020.9
8°	999.3
9°	976.6
10°	953.8
12.5°	887.8
15°	819.4
17.5°	751.0
20°	683.8
22.5°	615.4
25°	550.7
27.5°	485.9
30°	421.1
32.5°	357.5
35°	298.7
37.5°	248.3
40°	202.7
42.5°	160.8
45°	122.4
47.5°	92.4
50°	69.6
52.5°	51.6
55°	42.0
57.5°	37.2
60°	32.4
62.5°	28.8
65°	25.2
67.5°	21.6
70°	19.2
72.5°	15.6
75°	13.2
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)