

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268686

Luminaire Tested: P3AS02R409740DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409740DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 211.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268686
CATALOG NUMBER: P3AS02R409740DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1268686
 CATALOG NUMBER: P3AS02R409740DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47365
5°	46511
10°	43842
15°	39819
20°	34980
25°	29881
30°	24738
35°	19086
40°	13568
45°	9148
50°	4981
55°	3517
60°	3333
65°	3061
70°	2693
75°	2626
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9148 cd/sqm



TEST NUMBER: P1268686
 CATALOG NUMBER: P3AS02R409740DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.7	9.3
10°-20°	48.9	23.2
20°-30°	56.5	26.8
30°-40°	44.5	21.1
40°-50°	22.8	10.8
50°-60°	8.7	4.1
60°-70°	5.8	2.7
70°-80°	3.2	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	125.0	59.3
0°-40°	169.5	80.3
0°-60°	201.1	95.3
0°-90°	211.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	211.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	211	20
15°	175	49
25°	124	56
35°	71	45
45°	30	23
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1268686

CATALOG NUMBER: P3AS02R409740DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.0
2.5°	214.8
5°	211.3
7.5°	205.1
10°	196.9
12.5°	187.2
15°	175.4
17.5°	163.1
20°	149.9
22.5°	136.4
25°	123.5
27.5°	110.5
30°	97.7
32.5°	84.7
35°	71.3
37.5°	58.8
40°	47.4
42.5°	37.8
45°	29.5
47.5°	21.5
50°	14.6
52.5°	10.6
55°	9.2
57.5°	8.3
60°	7.6
62.5°	6.6
65°	5.9
67.5°	5.0
70°	4.2
72.5°	3.5
75°	3.1
77.5°	2.4
80°	1.7
82.5°	1.4
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)