

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268694

Luminaire Tested: P3AS02R409740DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268694
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409740DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 275.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268694

CATALOG NUMBER: P3AS02R409740DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1268694

CATALOG NUMBER: P3AS02R409740DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121679
5°	118159
10°	107212
15°	88582
20°	63892
25°	39510
30°	21396
35°	11056
40°	6011
45°	3380
50°	1706
55°	1262
60°	1140
65°	1090
70°	1090
75°	1017
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3380 cd/sqm

TEST NUMBER: P1268694

CATALOG NUMBER: P3AS02R409740DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	18.0
10°-20°	106.2	38.6
20°-30°	75.8	27.6
30°-40°	27.9	10.1
40°-50°	8.8	3.2
50°-60°	3.1	1.1
60°-70°	2.1	0.8
70°-80°	1.2	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.5	84.2
0°-40°	259.4	94.3
0°-60°	271.3	98.7
0°-90°	275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	555	
5°	537	49
15°	390	106
25°	163	76
35°	41	28
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268694

CATALOG NUMBER: P3AS02R409740DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	554.9
2.5°	550.7
5°	536.8
7.5°	513.6
10°	481.5
12.5°	440.7
15°	390.2
17.5°	333.5
20°	273.8
22.5°	215.0
25°	163.3
27.5°	119.9
30°	84.5
32.5°	59.2
35°	41.3
37.5°	29.3
40°	21.0
42.5°	15.1
45°	10.9
47.5°	7.3
50°	5.0
52.5°	3.5
55°	3.3
57.5°	3.1
60°	2.6
62.5°	2.4
65°	2.1
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.2
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)