

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267713

Luminaire Tested: P3AS17R159735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267713

CATALOG NUMBER: P3AS17R159735DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267713

CATALOG NUMBER: P3AS17R159735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230179
5°	215782
10°	176951
15°	137458
20°	108509
25°	86473
30°	69403
35°	56670
40°	46687
45°	39291
50°	33739
55°	29170
60°	25875
65°	22519
70°	20003
75°	16182
80°	13133
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 39291 cd/sqm

TEST NUMBER: P1267713

CATALOG NUMBER: P3AS17R159735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	11.1
10°-20°	169.6	21.4
20°-30°	164.8	20.8
30°-40°	133.3	16.8
40°-50°	98.9	12.5
50°-60°	69.1	8.7
60°-70°	43.3	5.5
70°-80°	20.6	2.6
80°-90°	3.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.0	53.4
0°-40°	555.3	70.2
0°-60°	723.4	91.4
0°-90°	791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1050	
5°	980	88
15°	606	170
25°	357	165
35°	212	133
45°	127	99
55°	76	69
65°	43	43
75°	19	21
85°	4	4
90°	0	

TEST NUMBER: P1267713

CATALOG NUMBER: P3AS17R159735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1049.7
2.5°	1032.4
5°	980.3
7.5°	897.0
10°	794.7
12.5°	694.0
15°	605.5
17.5°	530.9
20°	465.0
22.5°	407.7
25°	357.4
27.5°	312.3
30°	274.1
32.5°	241.2
35°	211.7
37.5°	185.7
40°	163.1
42.5°	144.0
45°	126.7
47.5°	112.8
50°	98.9
52.5°	86.8
55°	76.3
57.5°	67.7
60°	59.0
62.5°	50.3
65°	43.4
67.5°	36.4
70°	31.2
72.5°	24.3
75°	19.1
77.5°	13.9
80°	10.4
82.5°	5.2
85°	3.5
87.5°	0.0
90°	0.0

(END OF REPORT)