

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267726

Luminaire Tested: P3AS17R209735DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209735DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 608.0 lumens
Efficiency: N/A
Efficacy: 28.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267726

CATALOG NUMBER: P3AS17R209735DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1267726

CATALOG NUMBER: P3AS17R209735DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91		94	92	89		92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86		91	88	85		89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82		87	84	81		86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78		84	81	78		83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75		81	78	75		80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72		78	75	72		78	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70		76	72	69		75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67		73	70	67		73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467791
5°	425225
10°	314267
15°	194417
20°	111030
25°	63391
30°	35550
35°	19327
40°	10591
45°	5830
50°	3411
55°	2485
60°	2324
65°	2127
70°	1859
75°	1949
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5830 cd/sqm

TEST NUMBER: P1267726

CATALOG NUMBER: P3AS17R209735DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	27.5
10°-20°	238.8	39.3
20°-30°	124.6	20.5
30°-40°	48.2	7.9
40°-50°	15.6	2.6
50°-60°	6.2	1.0
60°-70°	4.1	0.7
70°-80°	2.4	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.7	87.3
0°-40°	578.9	95.2
0°-60°	600.7	98.8
0°-90°	608.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	608.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2133	
5°	1932	167
15°	856	239
25°	262	125
35°	72	48
45°	19	16
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1267726

CATALOG NUMBER: P3AS17R209735DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2133.3
1°	2129.2
2°	2103.9
3°	2065.1
4°	2005.2
5°	1931.8
6°	1844.9
7°	1748.6
8°	1637.0
9°	1528.3
10°	1411.4
12.5°	1121.9
15°	856.4
17.5°	640.8
20°	475.8
22.5°	352.4
25°	262.0
27.5°	193.2
30°	140.4
32.5°	101.6
35°	72.2
37.5°	52.3
40°	37.0
42.5°	26.4
45°	18.8
47.5°	13.5
50°	10.0
52.5°	7.6
55°	6.5
57.5°	5.9
60°	5.3
62.5°	4.7
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.9
75°	2.3
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)