

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268709

Luminaire Tested: P3AS02R459740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 100.0 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268709
CATALOG NUMBER: P3AS02R459740DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1268709
 CATALOG NUMBER: P3AS02R459740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 | | | |
| 2 | 106 | 100 | 95 | 91 | 103 | 98 | 94 | 90 | 95 | 91 | 88 | 92 | 89 | 86 | 89 | 87 | 85 | 83 | | | |
| 3 | 99 | 92 | 86 | 82 | 97 | 91 | 85 | 81 | 88 | 83 | 80 | 85 | 81 | 78 | 83 | 80 | 77 | 75 | | | |
| 4 | 94 | 85 | 78 | 74 | 92 | 84 | 78 | 73 | 81 | 76 | 72 | 79 | 75 | 71 | 77 | 74 | 71 | 69 | | | |
| 5 | 88 | 79 | 72 | 67 | 86 | 78 | 71 | 67 | 76 | 70 | 66 | 74 | 69 | 65 | 72 | 68 | 65 | 63 | | | |
| 6 | 83 | 73 | 66 | 61 | 81 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 | | | |
| 7 | 78 | 68 | 61 | 57 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 55 | 54 | | | |
| 8 | 74 | 64 | 57 | 52 | 73 | 63 | 57 | 52 | 62 | 56 | 52 | 61 | 56 | 52 | 60 | 55 | 52 | 50 | | | |
| 9 | 70 | 60 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 52 | 48 | 47 | | | |
| 10 | 67 | 56 | 50 | 45 | 66 | 56 | 49 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 44 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 21204 |
| 5° | 20823 |
| 10° | 19706 |
| 15° | 17980 |
| 20° | 15891 |
| 25° | 13791 |
| 30° | 11850 |
| 35° | 9878 |
| 40° | 7357 |
| 45° | 4497 |
| 50° | 2081 |
| 55° | 1644 |
| 60° | 1579 |
| 65° | 1453 |
| 70° | 1346 |
| 75° | 1271 |
| 80° | 1137 |
| 85° | 755 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4497 cd/sqm



TEST NUMBER: P1268709
 CATALOG NUMBER: P3AS02R459740DE010 E3DLD1GPH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 8.8 | 8.8 |
| 10°-20° | 22.0 | 22.0 |
| 20°-30° | 26.2 | 26.2 |
| 30°-40° | 22.8 | 22.8 |
| 40°-50° | 11.4 | 11.4 |
| 50°-60° | 4.0 | 4.0 |
| 60°-70° | 2.8 | 2.8 |
| 70°-80° | 1.6 | 1.6 |
| 80°-90° | 0.4 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 57.1 | 57.1 |
| 0°-40° | 79.8 | 79.8 |
| 0°-60° | 95.2 | 95.2 |
| 0°-90° | 100.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 100.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|----|------|
| 0° | 97 | |
| 5° | 95 | 9 |
| 15° | 79 | 22 |
| 25° | 57 | 26 |
| 35° | 37 | 23 |
| 45° | 14 | 11 |
| 55° | 4 | 4 |
| 65° | 3 | 3 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1268709
CATALOG NUMBER: P3AS02R459740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|------|
| 0° | 96.7 |
| 2.5° | 96.2 |
| 5° | 94.6 |
| 7.5° | 92.1 |
| 10° | 88.5 |
| 12.5° | 84.1 |
| 15° | 79.2 |
| 17.5° | 73.6 |
| 20° | 68.1 |
| 22.5° | 62.5 |
| 25° | 57.0 |
| 27.5° | 51.9 |
| 30° | 46.8 |
| 32.5° | 41.9 |
| 35° | 36.9 |
| 37.5° | 31.5 |
| 40° | 25.7 |
| 42.5° | 20.1 |
| 45° | 14.5 |
| 47.5° | 9.6 |
| 50° | 6.1 |
| 52.5° | 4.7 |
| 55° | 4.3 |
| 57.5° | 3.9 |
| 60° | 3.6 |
| 62.5° | 3.2 |
| 65° | 2.8 |
| 67.5° | 2.4 |
| 70° | 2.1 |
| 72.5° | 1.7 |
| 75° | 1.5 |
| 77.5° | 1.2 |
| 80° | 0.9 |
| 82.5° | 0.7 |
| 85° | 0.3 |
| 87.5° | 0.2 |
| 90° | 0.0 |

(END OF REPORT)