

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268715

Luminaire Tested: P3AS02R459740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 83.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268715

CATALOG NUMBER: P3AS02R459740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268715

CATALOG NUMBER: P3AS02R459740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	86	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24713
5°	24169
10°	22289
15°	19387
20°	15915
25°	12388
30°	9141
35°	6425
40°	4008
45°	2171
50°	1194
55°	994
60°	921
65°	778
70°	641
75°	678
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2171 cd/sqm

TEST NUMBER: P1268715

CATALOG NUMBER: P3AS02R459740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.2	12.3
10°-20°	23.6	28.4
20°-30°	23.4	28.2
30°-40°	15.1	18.2
40°-50°	5.8	7.0
50°-60°	2.4	2.9
60°-70°	1.5	1.8
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	57.2	68.9
0°-40°	72.3	87.1
0°-60°	80.4	96.9
0°-90°	83.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	83.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	113	
5°	110	10
15°	85	24
25°	51	23
35°	24	15
45°	7	6
55°	3	2
65°	2	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268715

CATALOG NUMBER: P3AS02R459740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	112.7
2.5°	112.2
5°	109.8
7.5°	105.6
10°	100.1
12.5°	93.2
15°	85.4
17.5°	76.8
20°	68.2
22.5°	59.5
25°	51.2
27.5°	43.4
30°	36.1
32.5°	29.8
35°	24.0
37.5°	18.9
40°	14.0
42.5°	10.1
45°	7.0
47.5°	4.7
50°	3.5
52.5°	2.9
55°	2.6
57.5°	2.3
60°	2.1
62.5°	1.7
65°	1.5
67.5°	1.3
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.5
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)