

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267740

Luminaire Tested: P3AS17R209735DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209735DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 27.7 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267740
CATALOG NUMBER: P3AS17R209735DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1267740
 CATALOG NUMBER: P3AS17R209735DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208733
5°	194717
10°	161565
15°	123542
20°	92735
25°	69802
30°	51628
35°	36085
40°	24732
45°	17149
50°	14737
55°	14528
60°	15174
65°	15255
70°	15515
75°	16097
80°	17426
85°	17360

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 20328 cd/sqm



TEST NUMBER: P1267740
 CATALOG NUMBER: P3AS17R209735DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.2	13.5
10°-20°	151.3	25.8
20°-30°	133.1	22.7
30°-40°	85.9	14.6
40°-50°	45.6	7.8
50°-60°	34.2	5.8
60°-70°	29.1	5.0
70°-80°	20.5	3.5
80°-90°	8.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.7	62.0
0°-40°	449.6	76.6
0°-60°	529.4	90.2
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	885	79
15°	544	151
25°	288	133
35°	135	86
45°	55	46
55°	38	34
65°	29	29
75°	19	21
85°	7	8
90°	0	



TEST NUMBER: P1267740
CATALOG NUMBER: P3AS17R209735DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	951.9
2.5°	932.9
5°	884.6
7.5°	810.3
10°	725.6
12.5°	632.3
15°	544.2
17.5°	464.7
20°	397.4
22.5°	340.4
25°	288.5
27.5°	243.6
30°	203.9
32.5°	167.6
35°	134.8
37.5°	108.8
40°	86.4
42.5°	69.1
45°	55.3
47.5°	48.4
50°	43.2
52.5°	39.7
55°	38.0
57.5°	36.3
60°	34.6
62.5°	31.1
65°	29.4
67.5°	27.6
70°	24.2
72.5°	22.5
75°	19.0
77.5°	17.3
80°	13.8
82.5°	12.1
85°	6.9
87.5°	3.5
90°	0.0

(END OF REPORT)