

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267772

Luminaire Tested: P3AS17R259735DE010 E3PHLP1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1267772  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R259735DE010 E3PHLP1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 692.0 lumens  
Efficiency: N/A  
Efficacy: 32.6 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1267772  
CATALOG NUMBER: P3AS17R259735DE010 E3PHLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1267772  
 CATALOG NUMBER: P3AS17R259735DE010 E3PHLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68	68	68	68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63	63	63	63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59	59	59	59
7	79	69	63	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	232503
5°	219678
10°	186726
15°	147901
20°	112406
25°	83835
30°	60971
35°	43125
40°	29255
45°	20405
50°	17125
55°	16554
60°	17455
65°	18005
70°	17759
75°	19063
80°	21846
85°	21889

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 23352 cd/sqm



TEST NUMBER: P1267772  
 CATALOG NUMBER: P3AS17R259735DE010 E3PHLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.1	13.0
10°-20°	180.3	26.1
20°-30°	159.7	23.1
30°-40°	101.7	14.7
40°-50°	53.8	7.8
50°-60°	39.5	5.7
60°-70°	33.7	4.9
70°-80°	23.8	3.4
80°-90°	9.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.1	62.1
0°-40°	531.8	76.8
0°-60°	625.1	90.3
0°-90°	692.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	692.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1060	
5°	998	90
15°	652	180
25°	346	160
35°	161	102
45°	66	54
55°	43	40
65°	35	34
75°	22	24
85°	9	9
90°	0	



TEST NUMBER: P1267772  
CATALOG NUMBER: P3AS17R259735DE010 E3PHLP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1060.3
2.5°	1044.8
5°	998.0
7.5°	925.2
10°	838.6
12.5°	745.0
15°	651.5
17.5°	561.4
20°	481.7
22.5°	408.9
25°	346.5
27.5°	291.1
30°	240.8
32.5°	197.5
35°	161.1
37.5°	128.2
40°	102.2
42.5°	81.4
45°	65.8
47.5°	57.2
50°	50.2
52.5°	46.8
55°	43.3
57.5°	41.6
60°	39.8
62.5°	36.4
65°	34.7
67.5°	31.2
70°	27.7
72.5°	26.0
75°	22.5
77.5°	19.1
80°	17.3
82.5°	13.9
85°	8.7
87.5°	3.5
90°	0.0

(END OF REPORT)