

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267849

Luminaire Tested: P3AS17R409735DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409735DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1397.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267849
CATALOG NUMBER: P3AS17R409735DE010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1267849
 CATALOG NUMBER: P3AS17R409735DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94				94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89				89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84				84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65				65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63				63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60				60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	618152
5°	600197
10°	544657
15°	449969
20°	324572
25°	200770
30°	108700
35°	56162
40°	30543
45°	17118
50°	8597
55°	6423
60°	5789
65°	5604
70°	5386
75°	5083
80°	4546
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17118 cd/sqm



TEST NUMBER: P1267849
 CATALOG NUMBER: P3AS17R409735DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.3	18.0
10°-20°	539.7	38.6
20°-30°	385.2	27.6
30°-40°	141.8	10.1
40°-50°	44.7	3.2
50°-60°	15.5	1.1
60°-70°	10.7	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1176.2	84.2
0°-40°	1318.0	94.3
0°-60°	1378.2	98.7
0°-90°	1397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1397.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2819	
5°	2727	251
15°	1982	540
25°	830	385
35°	210	142
45°	55	45
55°	17	16
65°	11	11
75°	6	6
85°	1	2
90°	0	

TEST NUMBER: P1267849

CATALOG NUMBER: P3AS17R409735DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2819.0
2.5°	2797.5
5°	2726.7
7.5°	2609.2
10°	2446.1
12.5°	2238.7
15°	1982.1
17.5°	1694.3
20°	1390.9
22.5°	1092.4
25°	829.8
27.5°	609.1
30°	429.3
32.5°	301.0
35°	209.8
37.5°	148.7
40°	106.7
42.5°	76.7
45°	55.2
47.5°	37.2
50°	25.2
52.5°	18.0
55°	16.8
57.5°	15.6
60°	13.2
62.5°	12.0
65°	10.8
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)