

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268862

Luminaire Tested: P3AS05R109740DE010 E3B1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109740DE010 E3B1GPH
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 97CRI , E3B1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 543.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.18 / 0.18 / 0.18
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268862

CATALOG NUMBER: P3AS05R109740DE010 E3B1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268862

CATALOG NUMBER: P3AS05R109740DE010 E3B1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100
2	113	110	108	106	111	109	107	105	106	104	103	103	102	101	100	99	98
3	111	107	104	102	109	106	103	101	104	102	100	101	100	98	99	98	97
4	109	105	102	99	107	104	101	99	102	99	98	100	98	97	98	97	96
5	107	102	99	97	105	101	99	97	100	98	96	99	97	95	97	96	94
6	105	100	97	95	104	100	97	95	98	96	94	97	95	94	96	95	93
7	103	99	96	93	102	98	95	93	97	95	93	96	94	92	95	93	92
8																	

TEST NUMBER: P1268862

CATALOG NUMBER: P3AS05R109740DE010 E3B1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.1	71.5
10°-20°	110.3	20.3
20°-30°	32.2	5.9
30°-40°	10.5	1.9
40°-50°	1.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.6	97.7
0°-40°	541.1	99.7
0°-60°	543.0	100.0
0°-90°	543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	543.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11212	
5°	5770	388
15°	346	110
25°	63	32
35°	16	11
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268862

CATALOG NUMBER: P3AS05R109740DE010 E3B1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11212.1
1°	10889.2
2°	10044.4
3°	8718.9
4°	7269.7
5°	5770.2
6°	4351.4
7°	3151.4
8°	2217.0
9°	1558.7
10°	1121.0
11°	830.5
12°	638.5
13°	513.0
14°	417.9
15°	346.2
17.5°	229.6
20°	147.1
22.5°	93.3
25°	62.8
27.5°	44.8
30°	32.3
32.5°	23.3
35°	16.1
37.5°	10.8
40°	5.4
42.5°	3.6
45°	1.8
47.5°	1.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1268862

CATALOG NUMBER: P3AS05R109740DE010 E3B1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)