

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267915

Luminaire Tested: P3AS17R509735DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509735DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 886.0 lumens
Efficiency: N/A
Efficacy: 41.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267915

CATALOG NUMBER: P3AS17R509735DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1267915

CATALOG NUMBER: P3AS17R509735DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		79
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		73
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257699
5°	250759
10°	231236
15°	203361
20°	170138
25°	134911
30°	98977
35°	68047
40°	43252
45°	24158
50°	13100
55°	11010
60°	9473
65°	8717
70°	7694
75°	7117
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24158 cd/sqm

TEST NUMBER: P1267915

CATALOG NUMBER: P3AS17R509735DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	11.9
10°-20°	248.1	28.0
20°-30°	253.8	28.6
30°-40°	160.9	18.2
40°-50°	64.0	7.2
50°-60°	26.0	2.9
60°-70°	16.6	1.9
70°-80°	8.5	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.4	68.5
0°-40°	768.3	86.7
0°-60°	858.3	96.9
0°-90°	886.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	886.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1175	
5°	1139	106
15°	896	248
25°	558	254
35°	254	161
45°	78	64
55°	29	26
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1267915

CATALOG NUMBER: P3AS17R509735DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1175.2
2.5°	1166.8
5°	1139.2
7.5°	1096.0
10°	1038.5
12.5°	970.1
15°	895.8
17.5°	814.2
20°	729.1
22.5°	643.9
25°	557.6
27.5°	471.3
30°	390.9
32.5°	319.0
35°	254.2
37.5°	199.1
40°	151.1
42.5°	111.5
45°	77.9
47.5°	52.8
50°	38.4
52.5°	32.4
55°	28.8
57.5°	25.2
60°	21.6
62.5°	19.2
65°	16.8
67.5°	14.4
70°	12.0
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)