

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267976

Luminaire Tested: P3AS17R659735DE010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659735DE010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1484.0 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267976

CATALOG NUMBER: P3AS17R659735DE010 E3CB1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1267976

CATALOG NUMBER: P3AS17R659735DE010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	362646
5°	341315
10°	336979
15°	331035
20°	312554
25°	290097
30°	225478
35°	130446
40°	52556
45°	24189
50°	9415
55°	3670
60°	3158
65°	3113
70°	3077
75°	3050
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24189 cd/sqm

TEST NUMBER: P1267976

CATALOG NUMBER: P3AS17R659735DE010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.4	9.9
10°-20°	407.2	27.4
20°-30°	533.1	35.9
30°-40°	308.8	20.8
40°-50°	66.1	4.5
50°-60°	10.8	0.7
60°-70°	5.9	0.4
70°-80°	3.5	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.7	73.3
0°-40°	1396.4	94.1
0°-60°	1473.3	99.3
0°-90°	1484.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1484.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1654	
5°	1551	147
15°	1458	407
25°	1199	533
35°	487	309
45°	78	66
55°	10	11
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1267976

CATALOG NUMBER: P3AS17R659735DE010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1653.8
2.5°	1607.0
5°	1550.6
7.5°	1527.8
10°	1513.4
12.5°	1493.0
15°	1458.2
17.5°	1404.2
20°	1339.4
22.5°	1278.2
25°	1199.0
27.5°	1065.8
30°	890.5
32.5°	690.1
35°	487.3
37.5°	308.4
40°	183.6
42.5°	115.2
45°	78.0
47.5°	50.4
50°	27.6
52.5°	13.2
55°	9.6
57.5°	8.4
60°	7.2
62.5°	7.2
65°	6.0
67.5°	4.8
70°	4.8
72.5°	3.6
75°	3.6
77.5°	2.4
80°	2.4
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)