

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268927

Luminaire Tested: P3AS05R129740DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268927
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129740DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 4000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 257.0 lumens
Efficiency: N/A
Efficacy: 33.8 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268927
CATALOG NUMBER: P3AS05R129740DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268927
 CATALOG NUMBER: P3AS05R129740DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90			90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96198
5°	88311
10°	70384
15°	52600
20°	39950
25°	30244
30°	22383
35°	15981
40°	10935
45°	7660
50°	6516
55°	6384
60°	6622
65°	7005
70°	7117
75°	7456
80°	8082
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 9408 cd/sqm



TEST NUMBER: P1268927
 CATALOG NUMBER: P3AS05R129740DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.5	13.8
10°-20°	65.0	25.3
20°-30°	57.6	22.4
30°-40°	37.7	14.7
40°-50°	20.2	7.8
50°-60°	15.2	5.9
60°-70°	13.1	5.1
70°-80°	9.1	3.5
80°-90°	3.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.1	61.5
0°-40°	195.8	76.2
0°-60°	231.2	89.9
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	439	
5°	401	36
15°	232	65
25°	125	58
35°	60	38
45°	25	20
55°	17	15
65°	14	13
75°	9	9
85°	3	4
90°	0	



TEST NUMBER: P1268927
CATALOG NUMBER: P3AS05R129740DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	438.7
2.5°	428.3
5°	401.2
7.5°	361.4
10°	316.1
12.5°	272.3
15°	231.7
17.5°	199.0
20°	171.2
22.5°	146.5
25°	125.0
27.5°	105.9
30°	88.4
32.5°	73.2
35°	59.7
37.5°	47.8
40°	38.2
42.5°	30.3
45°	24.7
47.5°	21.5
50°	19.1
52.5°	18.3
55°	16.7
57.5°	15.9
60°	15.1
62.5°	14.3
65°	13.5
67.5°	11.9
70°	11.1
72.5°	9.6
75°	8.8
77.5°	7.2
80°	6.4
82.5°	5.6
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)