

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1267980

Luminaire Tested: P3AS17R659735DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1267980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659735DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1431.0 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1267980

CATALOG NUMBER: P3AS17R659735DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1267980

CATALOG NUMBER: P3AS17R659735DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	88		93	89	86		90	87	85		88	86	83
4	98	91	85	81		96	90	85	81		87	83	80		85	82	79		84	81	78
5	93	85	79	75		92	84	79	75		82	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	69		76	72	69		75	71	68
7	84	75	70	65		83	75	69	65		73	69	65		72	68	65		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	67	61	58		76	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	57	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	383456
5°	356041
10°	344304
15°	331807
20°	306767
25°	279500
30°	215957
35°	125173
40°	49664
45°	21149
50°	5015
55°	688
60°	526
65°	311
70°	385
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21149 cd/sqm

TEST NUMBER: P1267980

CATALOG NUMBER: P3AS17R659735DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.5	10.7
10°-20°	407.3	28.5
20°-30°	515.5	36.0
30°-40°	293.5	20.5
40°-50°	58.3	4.1
50°-60°	3.0	0.2
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.3	75.1
0°-40°	1368.8	95.7
0°-60°	1430.1	99.9
0°-90°	1431.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1431.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1749	
5°	1618	153
15°	1462	407
25°	1155	515
35°	468	294
45°	68	58
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1267980

CATALOG NUMBER: P3AS17R659735DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1748.7
1°	1735.7
2°	1707.5
3°	1674.5
4°	1642.2
5°	1617.5
6°	1599.3
7°	1584.6
8°	1571.6
9°	1558.7
10°	1546.3
11°	1532.8
12°	1518.7
13°	1501.6
14°	1483.4
15°	1461.6
16°	1435.7
17°	1407.5
18°	1376.9
19°	1344.6
20°	1314.6
21°	1284.0
22°	1256.3
23°	1227.5
24°	1194.0
25°	1155.2
26°	1108.7
27°	1052.8
28°	989.9
29°	922.9
30°	852.9
31°	775.8
32°	699.3
32.5°	659.9
33°	621.7
34°	544.1
35°	467.6
36°	397.0
37°	327.0
37.5°	291.1
38°	262.3
39°	212.3
40°	173.5
42.5°	107.0
45°	68.2



TEST NUMBER: P1267980

CATALOG NUMBER: P3AS17R659735DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	40.0
50°	14.7
52.5°	2.9
55°	1.8
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)