

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268945

Luminaire Tested: P3AS05R159740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 188.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268945

CATALOG NUMBER: P3AS05R159740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268945

CATALOG NUMBER: P3AS05R159740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	70	63	58	78	69	63	58	67	62	58		66	61	58		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47430
5°	46137
10°	42150
15°	36936
20°	31689
25°	26445
30°	21168
35°	15874
40°	11536
45°	7536
50°	4708
55°	3173
60°	2807
65°	2594
70°	2436
75°	2203
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7536 cd/sqm

TEST NUMBER: P1268945

CATALOG NUMBER: P3AS05R159740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.3	10.3
10°-20°	45.3	24.1
20°-30°	49.9	26.6
30°-40°	37.4	19.9
40°-50°	19.4	10.3
50°-60°	8.0	4.3
60°-70°	5.0	2.6
70°-80°	2.8	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.6	61.0
0°-40°	152.0	80.9
0°-60°	179.4	95.4
0°-90°	188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	188.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	210	19
15°	163	45
25°	109	50
35°	59	37
45°	24	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1268945

CATALOG NUMBER: P3AS05R159740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.3
1°	216.5
2°	215.8
3°	214.3
4°	212.2
5°	209.6
6°	206.3
7°	202.7
8°	198.4
9°	193.9
10°	189.3
12.5°	176.2
15°	162.7
17.5°	149.1
20°	135.8
22.5°	122.2
25°	109.3
27.5°	96.5
30°	83.6
32.5°	71.0
35°	59.3
37.5°	49.3
40°	40.3
42.5°	31.9
45°	24.3
47.5°	18.3
50°	13.8
52.5°	10.2
55°	8.3
57.5°	7.4
60°	6.4
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.8
72.5°	3.1
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)