

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268951

Luminaire Tested: P3AS05R159740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 146.0 lumens
Efficiency: N/A
Efficacy: 20.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268951

CATALOG NUMBER: P3AS05R159740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1268951

CATALOG NUMBER: P3AS05R159740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62955
5°	58199
10°	46448
15°	35097
20°	26719
25°	20372
30°	14585
35°	9530
40°	5840
45°	3535
50°	2354
55°	1797
60°	1579
65°	1349
70°	1218
75°	1186
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3535 cd/sqm

TEST NUMBER: P1268951

CATALOG NUMBER: P3AS05R159740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.4	16.0
10°-20°	43.2	29.6
20°-30°	38.5	26.3
30°-40°	22.8	15.6
40°-50°	9.4	6.4
50°-60°	4.4	3.0
60°-70°	2.7	1.8
70°-80°	1.4	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	105.1	72.0
0°-40°	127.9	87.6
0°-60°	141.6	97.0
0°-90°	146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	264	23
15°	155	43
25°	84	38
35°	36	23
45°	11	9
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1268951

CATALOG NUMBER: P3AS05R159740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	287.1
1°	286.4
2°	284.3
3°	280.0
4°	272.9
5°	264.4
6°	255.1
7°	244.2
8°	232.8
9°	221.2
10°	208.6
12.5°	179.9
15°	154.6
17.5°	132.8
20°	114.5
22.5°	98.4
25°	84.2
27.5°	70.4
30°	57.6
32.5°	46.0
35°	35.6
37.5°	27.3
40°	20.4
42.5°	15.2
45°	11.4
47.5°	8.8
50°	6.9
52.5°	5.7
55°	4.7
57.5°	4.0
60°	3.6
62.5°	3.1
65°	2.6
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.4
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)