

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268980

Luminaire Tested: P3AS05R209740DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209740DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 382.0 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268980

CATALOG NUMBER: P3AS05R209740DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1268980

CATALOG NUMBER: P3AS05R209740DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94488
5°	91965
10°	84590
15°	74461
20°	63869
25°	53664
30°	43374
35°	33006
40°	23473
45°	15505
50°	9586
55°	6308
60°	5745
65°	5292
70°	5001
75°	4490
80°	4293
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15505 cd/sqm

TEST NUMBER: P1268980

CATALOG NUMBER: P3AS05R209740DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	10.1
10°-20°	91.3	23.9
20°-30°	101.4	26.5
30°-40°	77.3	20.2
40°-50°	39.6	10.4
50°-60°	16.3	4.3
60°-70°	10.1	2.7
70°-80°	5.7	1.5
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	231.3	60.6
0°-40°	308.7	80.8
0°-60°	364.5	95.4
0°-90°	382.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	431	
5°	418	39
15°	328	91
25°	222	101
35°	123	77
45°	50	40
55°	16	16
65°	10	10
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1268980

CATALOG NUMBER: P3AS05R209740DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	430.9
1°	431.4
2°	429.4
3°	427.0
4°	423.1
5°	417.8
6°	411.5
7°	404.7
8°	397.4
9°	388.7
10°	379.9
12.5°	354.7
15°	328.0
17.5°	300.9
20°	273.7
22.5°	246.5
25°	221.8
27.5°	197.0
30°	171.3
32.5°	147.0
35°	123.3
37.5°	102.4
40°	82.0
42.5°	64.5
45°	50.0
47.5°	37.8
50°	28.1
52.5°	20.9
55°	16.5
57.5°	15.0
60°	13.1
62.5°	11.6
65°	10.2
67.5°	8.7
70°	7.8
72.5°	6.3
75°	5.3
77.5°	4.4
80°	3.4
82.5°	2.4
85°	1.5
87.5°	0.5
90°	0.0

(END OF REPORT)