

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268117

Luminaire Tested: P3AS20R209735D010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209735D010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1083.9 lumens
Efficiency: N/A
Efficacy: 37.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268117
CATALOG NUMBER: P3AS20R209735D010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1268117
 CATALOG NUMBER: P3AS20R209735D010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	72	72	72	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55	55	55	55
7	76	66	59	54	75	65	58	53	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47	47	47	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307432
5°	285581
10°	241835
15°	189309
20°	148996
25°	118749
30°	95508
35°	77845
40°	64378
45°	54269
50°	46497
55°	39951
60°	34866
65°	30665
70°	26222
75°	23130
80°	17174
85°	11322

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 54269 cd/sqm



TEST NUMBER: P1268117
 CATALOG NUMBER: P3AS20R209735D010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.1	10.8
10°-20°	233.5	21.5
20°-30°	226.7	20.9
30°-40°	183.1	16.9
40°-50°	136.1	12.6
50°-60°	94.5	8.7
60°-70°	59.2	5.5
70°-80°	28.7	2.7
80°-90°	4.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.3	53.3
0°-40°	760.4	70.2
0°-60°	991.1	91.4
0°-90°	1083.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1083.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1402	
5°	1297	117
15°	834	233
25°	491	227
35°	291	183
45°	175	136
55°	104	95
65°	59	59
75°	27	29
85°	4	5
90°	0	



TEST NUMBER: P1268117
CATALOG NUMBER: P3AS20R209735D010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1402.0
2.5°	1370.1
5°	1297.4
7.5°	1199.7
10°	1086.1
12.5°	961.1
15°	833.9
17.5°	729.4
20°	638.5
22.5°	559.0
25°	490.8
27.5°	431.7
30°	377.2
32.5°	331.7
35°	290.8
37.5°	254.5
40°	224.9
42.5°	197.7
45°	175.0
47.5°	154.5
50°	136.3
52.5°	120.4
55°	104.5
57.5°	90.9
60°	79.5
62.5°	70.4
65°	59.1
67.5°	50.0
70°	40.9
72.5°	34.1
75°	27.3
77.5°	20.4
80°	13.6
82.5°	6.8
85°	4.5
87.5°	0.0
90°	0.0

(END OF REPORT)