

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269045

Luminaire Tested: P3AS05R309740DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309740DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 514.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269045

CATALOG NUMBER: P3AS05R309740DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1269045

CATALOG NUMBER: P3AS05R309740DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		78
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299932
5°	285471
10°	240120
15°	173168
20°	107413
25°	61092
30°	33929
35°	18444
40°	9733
45°	5272
50°	2831
55°	1873
60°	1710
65°	1764
70°	1539
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5272 cd/sqm

TEST NUMBER: P1269045

CATALOG NUMBER: P3AS05R309740DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	22.7
10°-20°	207.6	40.4
20°-30°	120.0	23.3
30°-40°	45.5	8.9
40°-50°	14.0	2.7
50°-60°	4.7	0.9
60°-70°	3.2	0.6
70°-80°	1.7	0.3
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	444.3	86.4
0°-40°	489.9	95.3
0°-60°	508.6	98.9
0°-90°	514.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	514.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1368	
5°	1297	117
15°	763	208
25°	252	120
35°	69	46
45°	17	14
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1269045

CATALOG NUMBER: P3AS05R309740DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1367.8
1°	1366.8
2°	1358.6
3°	1343.0
4°	1323.6
5°	1296.9
6°	1262.9
7°	1225.1
8°	1182.8
9°	1132.3
10°	1078.4
11°	1020.2
12°	958.5
13°	893.9
14°	828.4
15°	762.8
17.5°	601.6
20°	460.3
22.5°	341.3
25°	252.5
27.5°	183.5
30°	134.0
32.5°	96.6
35°	68.9
37.5°	48.1
40°	34.0
42.5°	23.8
45°	17.0
47.5°	11.7
50°	8.3
52.5°	5.8
55°	4.9
57.5°	4.4
60°	3.9
62.5°	3.4
65°	3.4
67.5°	2.9
70°	2.4
72.5°	1.9
75°	1.5
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.0



TEST NUMBER: P1269045

CATALOG NUMBER: P3AS05R309740DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)