

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269092

Luminaire Tested: P3AS05R409740DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409740DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269092
CATALOG NUMBER: P3AS05R409740DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1269092
 CATALOG NUMBER: P3AS05R409740DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94				94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89				89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84				84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80				80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65				65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63				63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60				60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250002
5°	242746
10°	220281
15°	181976
20°	131261
25°	81198
30°	43956
35°	22727
40°	12366
45°	6915
50°	3480
55°	2600
60°	2324
65°	2283
70°	2180
75°	2033
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6915 cd/sqm



TEST NUMBER: P1269092
 CATALOG NUMBER: P3AS05R409740DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.7	18.0
10°-20°	218.3	38.6
20°-30°	155.8	27.6
30°-40°	57.3	10.1
40°-50°	18.0	3.2
50°-60°	6.3	1.1
60°-70°	4.3	0.8
70°-80°	2.5	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.7	84.2
0°-40°	533.1	94.3
0°-60°	557.4	98.7
0°-90°	565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1140	
5°	1103	102
15°	802	218
25°	336	156
35°	85	57
45°	22	18
55°	7	6
65°	4	4
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P1269092
CATALOG NUMBER: P3AS05R409740DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1140.1
2.5°	1131.4
5°	1102.8
7.5°	1055.3
10°	989.3
12.5°	905.4
15°	801.6
17.5°	685.2
20°	562.5
22.5°	441.8
25°	335.6
27.5°	246.4
30°	173.6
32.5°	121.7
35°	84.9
37.5°	60.1
40°	43.2
42.5°	31.0
45°	22.3
47.5°	15.0
50°	10.2
52.5°	7.3
55°	6.8
57.5°	6.3
60°	5.3
62.5°	4.8
65°	4.4
67.5°	3.9
70°	3.4
72.5°	2.9
75°	2.4
77.5°	1.9
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)