

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269095

Luminaire Tested: P3AS05R409740DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409740DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 212.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269095

CATALOG NUMBER: P3AS05R409740DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269095

CATALOG NUMBER: P3AS05R409740DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47584
5°	46731
10°	44043
15°	40000
20°	35143
25°	30002
30°	24865
35°	19167
40°	13654
45°	9179
50°	5015
55°	3555
60°	3333
65°	3061
70°	2757
75°	2626
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9179 cd/sqm

TEST NUMBER: P1269095

CATALOG NUMBER: P3AS05R409740DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.8	9.3
10°-20°	49.1	23.2
20°-30°	56.7	26.8
30°-40°	44.7	21.1
40°-50°	22.9	10.8
50°-60°	8.8	4.1
60°-70°	5.8	2.7
70°-80°	3.2	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	125.6	59.2
0°-40°	170.4	80.3
0°-60°	202.1	95.3
0°-90°	212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	212	20
15°	176	49
25°	124	57
35°	72	45
45°	30	23
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1269095

CATALOG NUMBER: P3AS05R409740DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	217.0
2.5°	215.8
5°	212.3
7.5°	206.1
10°	197.8
12.5°	188.1
15°	176.2
17.5°	163.9
20°	150.6
22.5°	137.1
25°	124.0
27.5°	111.0
30°	98.2
32.5°	85.2
35°	71.6
37.5°	59.1
40°	47.7
42.5°	37.9
45°	29.6
47.5°	21.6
50°	14.7
52.5°	10.7
55°	9.3
57.5°	8.3
60°	7.6
62.5°	6.6
65°	5.9
67.5°	5.0
70°	4.3
72.5°	3.6
75°	3.1
77.5°	2.4
80°	1.7
82.5°	1.4
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)