

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268241

Luminaire Tested: P3AS20R459735D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268241
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459735D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2112.1 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268241

CATALOG NUMBER: P3AS20R459735D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1268241

CATALOG NUMBER: P3AS20R459735D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	90	89
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86	85	84
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	81	80
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	78	77
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	74	73
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	71	70
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	65	64
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	915672
5°	920557
10°	892257
15°	747723
20°	571576
25°	347948
30°	144782
35°	46391
40°	14427
45°	2946
50°	2149
55°	2409
60°	2061
65°	2439
70°	2052
75°	2711
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2946 cd/sqm

TEST NUMBER: P1268241

CATALOG NUMBER: P3AS20R459735D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.4	18.7
10°-20°	905.3	42.9
20°-30°	651.8	30.9
30°-40°	135.6	6.4
40°-50°	12.4	0.6
50°-60°	5.1	0.2
60°-70°	4.1	0.2
70°-80°	2.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1951.5	92.4
0°-40°	2087.1	98.8
0°-60°	2104.6	99.6
0°-90°	2112.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2112.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4176	
5°	4182	394
15°	3294	905
25°	1438	652
35°	173	136
45°	10	12
55°	6	5
65°	5	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1268241

CATALOG NUMBER: P3AS20R459735D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4175.8
2.5°	4177.4
5°	4182.1
7.5°	4152.2
10°	4007.2
12.5°	3704.8
15°	3293.7
17.5°	2873.1
20°	2449.4
22.5°	1962.7
25°	1438.1
27.5°	948.3
30°	571.8
32.5°	319.8
35°	173.3
37.5°	97.7
40°	50.4
42.5°	22.1
45°	9.5
47.5°	6.3
50°	6.3
52.5°	6.3
55°	6.3
57.5°	4.7
60°	4.7
62.5°	4.7
65°	4.7
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)