

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269155

Luminaire Tested: P3AS05R509740DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509740DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 176.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269155

CATALOG NUMBER: P3AS05R509740DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1269155

CATALOG NUMBER: P3AS05R509740DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51180
5°	49813
10°	45935
15°	40386
20°	33790
25°	26808
30°	19674
35°	13518
40°	8588
45°	4807
50°	2593
55°	2179
60°	1886
65°	1712
70°	1539
75°	1440
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4807 cd/sqm

TEST NUMBER: P1269155

CATALOG NUMBER: P3AS05R509740DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	11.9
10°-20°	49.3	28.0
20°-30°	50.4	28.6
30°-40°	32.0	18.2
40°-50°	12.7	7.2
50°-60°	5.1	2.9
60°-70°	3.3	1.9
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.6	68.5
0°-40°	152.6	86.7
0°-60°	170.5	96.9
0°-90°	176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	176.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	233	
5°	226	21
15°	178	49
25°	111	50
35°	50	32
45°	16	13
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1269155

CATALOG NUMBER: P3AS05R509740DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	233.4
2.5°	231.8
5°	226.3
7.5°	217.7
10°	206.3
12.5°	192.7
15°	177.9
17.5°	161.7
20°	144.8
22.5°	127.9
25°	110.8
27.5°	93.6
30°	77.7
32.5°	63.4
35°	50.5
37.5°	39.5
40°	30.0
42.5°	22.2
45°	15.5
47.5°	10.5
50°	7.6
52.5°	6.4
55°	5.7
57.5°	5.0
60°	4.3
62.5°	3.8
65°	3.3
67.5°	2.9
70°	2.4
72.5°	1.9
75°	1.7
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)