

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269212

Luminaire Tested: P3AS05R609740DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269212
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609740DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 400.0 lumens
Efficiency: N/A
Efficacy: 55.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269212
CATALOG NUMBER: P3AS05R609740DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1269212
 CATALOG NUMBER: P3AS05R609740DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71003
5°	70218
10°	67779
15°	64041
20°	59015
25°	53447
30°	47450
35°	40555
40°	32232
45°	22731
50°	13577
55°	6881
60°	6578
65°	6071
70°	5578
75°	5338
80°	4925
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22731 cd/sqm



TEST NUMBER: P1269212

CATALOG NUMBER: P3AS05R609740DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.0	7.5
10°-20°	78.8	19.7
20°-30°	101.2	25.3
30°-40°	93.9	23.5
40°-50°	57.1	14.3
50°-60°	19.0	4.8
60°-70°	11.6	2.9
70°-80°	6.5	1.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.0	52.5
0°-40°	303.9	76.0
0°-60°	380.0	95.0
0°-90°	400.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	400.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	324	
5°	319	30
15°	282	79
25°	221	101
35°	152	94
45°	73	57
55°	18	19
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1269212
CATALOG NUMBER: P3AS05R609740DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	323.8
2.5°	322.4
5°	319.0
7.5°	312.6
10°	304.4
12.5°	294.2
15°	282.1
17.5°	268.0
20°	252.9
22.5°	236.9
25°	220.9
27.5°	204.4
30°	187.4
32.5°	170.4
35°	151.5
37.5°	131.6
40°	112.6
42.5°	92.7
45°	73.3
47.5°	56.8
50°	39.8
52.5°	23.8
55°	18.0
57.5°	16.5
60°	15.0
62.5°	13.1
65°	11.7
67.5°	10.2
70°	8.7
72.5°	7.3
75°	6.3
77.5°	4.9
80°	3.9
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)