

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269226

Luminaire Tested: P3AS05R659740DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659740DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 579.0 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269226
CATALOG NUMBER: P3AS05R659740DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1269226

CATALOG NUMBER: P3AS05R659740DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77				77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67				67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63				63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	68	63	60	59				59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52				52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155141
5°	144067
10°	139321
15°	134257
20°	124121
25°	113087
30°	87381
35°	50647
40°	20095
45°	8559
50°	2013
55°	268
60°	219
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8559 cd/sqm



TEST NUMBER: P1269226

CATALOG NUMBER: P3AS05R659740DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	10.7
10°-20°	164.8	28.5
20°-30°	208.6	36.0
30°-40°	118.8	20.5
40°-50°	23.6	4.1
50°-60°	1.2	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	435.1	75.1
0°-40°	553.8	95.7
0°-60°	578.6	99.9
0°-90°	579.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	579.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	708	
5°	654	62
15°	591	165
25°	467	209
35°	189	119
45°	28	24
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1269226

CATALOG NUMBER: P3AS05R659740DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	707.5
1°	702.3
2°	690.9
3°	677.5
4°	664.5
5°	654.5
6°	647.1
7°	641.1
8°	635.9
9°	630.7
10°	625.7
11°	620.2
12°	614.5
13°	607.6
14°	600.2
15°	591.4
16°	580.9
17°	569.5
18°	557.1
19°	544.0
20°	531.9
21°	519.5
22°	508.3
23°	496.7
24°	483.1
25°	467.4
26°	448.6
27°	426.0
28°	400.5
29°	373.4
30°	345.1
31°	313.9
32°	283.0
32.5°	267.0
33°	251.5
34°	220.1
35°	189.2
36°	160.6
37°	132.3
37.5°	117.8
38°	106.1
39°	85.9
40°	70.2
42.5°	43.3
45°	27.6



TEST NUMBER: P1269226
CATALOG NUMBER: P3AS05R659740DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.2
50°	5.9
52.5°	1.2
55°	0.7
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)