

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268330

Luminaire Tested: P3AS20R609735D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609735D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1887.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268330

CATALOG NUMBER: P3AS20R609735D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1268330

CATALOG NUMBER: P3AS20R609735D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	71	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494412
5°	466739
10°	454612
15°	444225
20°	413036
25°	369239
30°	282043
35°	162837
40°	63204
45°	26328
50°	5799
55°	879
60°	658
65°	415
70°	513
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26328 cd/sqm

TEST NUMBER: P1268330

CATALOG NUMBER: P3AS20R609735D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.2	10.6
10°-20°	545.1	28.9
20°-30°	682.7	36.2
30°-40°	381.7	20.2
40°-50°	72.5	3.8
50°-60°	3.7	0.2
60°-70°	0.9	0.0
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1427.9	75.7
0°-40°	1809.6	95.9
0°-60°	1885.8	99.9
0°-90°	1887.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1887.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2255	
5°	2120	200
15°	1957	545
25°	1526	683
35°	608	382
45°	85	73
55°	2	4
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1268330

CATALOG NUMBER: P3AS20R609735D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2254.7
1°	2245.5
2°	2216.1
3°	2181.4
4°	2149.0
5°	2120.4
6°	2098.8
7°	2080.3
8°	2066.4
9°	2053.3
10°	2041.7
11°	2030.1
12°	2017.0
13°	2000.8
14°	1981.5
15°	1956.8
16°	1926.7
17°	1892.7
18°	1854.1
19°	1810.1
20°	1770.0
21°	1726.8
22°	1682.0
23°	1634.9
24°	1583.2
25°	1526.1
26°	1458.9
27°	1384.0
28°	1299.9
29°	1210.3
30°	1113.9
31°	1016.6
32°	916.3
32.5°	861.4
33°	812.0
34°	709.4
35°	608.3
36°	517.2
37°	420.7
37.5°	376.7
38°	333.5
39°	268.6
40°	220.8
42.5°	134.3
45°	84.9



TEST NUMBER: P1268330
CATALOG NUMBER: P3AS20R609735D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	47.1
50°	17.0
52.5°	3.9
55°	2.3
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)