

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269237

Luminaire Tested: P3AS05R659740DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659740DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 382.1 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269237

CATALOG NUMBER: P3AS05R659740DE010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269237

CATALOG NUMBER: P3AS05R659740DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67977
5°	67070
10°	64817
15°	61135
20°	56378
25°	51172
30°	45323
35°	38574
40°	30686
45°	21677
50°	12588
55°	6881
60°	6403
65°	5811
70°	5257
75°	4914
80°	4293
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21677 cd/sqm

TEST NUMBER: P1269237

CATALOG NUMBER: P3AS05R659740DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.7	7.5
10°-20°	75.3	19.7
20°-30°	96.8	25.3
30°-40°	89.5	23.4
40°-50°	54.1	14.2
50°-60°	18.5	4.8
60°-70°	11.1	2.9
70°-80°	6.3	1.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	200.8	52.6
0°-40°	290.3	76.0
0°-60°	362.9	95.0
0°-90°	382.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	310	
5°	305	29
15°	269	75
25°	212	97
35°	144	90
45°	70	54
55°	18	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1269237

CATALOG NUMBER: P3AS05R659740DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	310.0
2.5°	308.6
5°	304.7
7.5°	298.8
10°	291.1
12.5°	281.4
15°	269.3
17.5°	256.2
20°	241.6
22.5°	226.6
25°	211.5
27.5°	195.5
30°	179.0
32.5°	162.5
35°	144.1
37.5°	126.1
40°	107.2
42.5°	88.3
45°	69.9
47.5°	52.9
50°	36.9
52.5°	23.3
55°	18.0
57.5°	16.0
60°	14.6
62.5°	12.6
65°	11.2
67.5°	9.7
70°	8.2
72.5°	7.3
75°	5.8
77.5°	4.9
80°	3.4
82.5°	2.4
85°	1.5
87.5°	1.0
90°	0.0

(END OF REPORT)