

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1268370

Luminaire Tested: P3AS20R659735D010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1268370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659735D010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1240.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1268370

CATALOG NUMBER: P3AS20R659735D010 E3DLD1H

Luminous Intensity Polar Plot



TEST NUMBER: P1268370

CATALOG NUMBER: P3AS20R659735D010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	220662
5°	217697
10°	210395
15°	198412
20°	183019
25°	166122
30°	147137
35°	125200
40°	99615
45°	70333
50°	40834
55°	22288
60°	20700
65°	18783
70°	17182
75°	16013
80°	13891
85°	11825

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 70333 cd/sqm

TEST NUMBER: P1268370

CATALOG NUMBER: P3AS20R659735D010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.0	7.5
10°-20°	244.5	19.7
20°-30°	314.3	25.3
30°-40°	290.7	23.4
40°-50°	175.5	14.2
50°-60°	59.9	4.8
60°-70°	36.0	2.9
70°-80°	20.3	1.6
80°-90°	5.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.8	52.6
0°-40°	942.5	76.0
0°-60°	1177.9	95.0
0°-90°	1240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1006	
5°	989	93
15°	874	245
25°	687	314
35°	468	291
45°	227	175
55°	58	60
65°	36	36
75°	19	20
85°	5	6
90°	0	

TEST NUMBER: P1268370

CATALOG NUMBER: P3AS20R659735D010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1006.3
2.5°	1001.6
5°	989.0
7.5°	970.1
10°	944.9
12.5°	913.4
15°	874.0
17.5°	831.5
20°	784.3
22.5°	735.4
25°	686.6
27.5°	634.7
30°	581.1
32.5°	527.6
35°	467.7
37.5°	409.5
40°	348.0
42.5°	286.6
45°	226.8
47.5°	171.7
50°	119.7
52.5°	75.6
55°	58.3
57.5°	52.0
60°	47.2
62.5°	40.9
65°	36.2
67.5°	31.5
70°	26.8
72.5°	23.6
75°	18.9
77.5°	15.7
80°	11.0
82.5°	7.9
85°	4.7
87.5°	3.1
90°	0.0

(END OF REPORT)