

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269251

Luminaire Tested: P3AS05R709740DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709740DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269251

CATALOG NUMBER: P3AS05R709740DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1269251

CATALOG NUMBER: P3AS05R709740DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120539
5°	115012
10°	109439
15°	106493
20°	102559
25°	97070
30°	90292
35°	75837
40°	48892
45°	22731
50°	5970
55°	1491
60°	1491
65°	1245
70°	1218
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22731 cd/sqm

TEST NUMBER: P1269251

CATALOG NUMBER: P3AS05R709740DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.9	8.1
10°-20°	131.8	21.7
20°-30°	184.2	30.3
30°-40°	170.8	28.1
40°-50°	61.2	10.1
50°-60°	5.2	0.9
60°-70°	2.6	0.4
70°-80°	1.7	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.9	60.1
0°-40°	535.7	88.2
0°-60°	602.1	99.2
0°-90°	607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	550	
5°	522	49
15°	469	132
25°	401	184
35°	283	171
45°	73	61
55°	4	5
65°	2	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1269251

CATALOG NUMBER: P3AS05R709740DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	549.7
2.5°	541.4
5°	522.5
7.5°	505.0
10°	491.5
12.5°	480.3
15°	469.1
17.5°	455.6
20°	439.5
22.5°	421.1
25°	401.2
27.5°	380.8
30°	356.6
32.5°	325.5
35°	283.3
37.5°	229.5
40°	170.8
42.5°	116.4
45°	73.3
47.5°	40.8
50°	17.5
52.5°	5.8
55°	3.9
57.5°	3.4
60°	3.4
62.5°	2.9
65°	2.4
67.5°	2.4
70°	1.9
72.5°	1.9
75°	1.5
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)