

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269260

Luminaire Tested: P3AS05R709740DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709740DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 488.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269260

CATALOG NUMBER: P3AS05R709740DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1269260

CATALOG NUMBER: P3AS05R709740DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77			
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70			
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65			
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94466
5°	93330
10°	90646
15°	86811
20°	81300
25°	73867
30°	63807
35°	50862
40°	37041
45°	24344
50°	11394
55°	3517
60°	3421
65°	3269
70°	3077
75°	3304
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24344 cd/sqm

TEST NUMBER: P1269260

CATALOG NUMBER: P3AS05R709740DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.9	8.2
10°-20°	107.0	21.9
20°-30°	139.1	28.5
30°-40°	118.0	24.2
40°-50°	60.9	12.5
50°-60°	11.7	2.4
60°-70°	6.4	1.3
70°-80°	3.9	0.8
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.0	58.6
0°-40°	404.1	82.8
0°-60°	476.6	97.7
0°-90°	488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	431	
5°	424	40
15°	382	107
25°	305	139
35°	190	118
45°	78	61
55°	9	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1269260

CATALOG NUMBER: P3AS05R709740DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	430.8
2.5°	429.4
5°	424.0
7.5°	416.3
10°	407.1
12.5°	395.5
15°	382.4
17.5°	366.4
20°	348.4
22.5°	328.1
25°	305.3
27.5°	279.6
30°	252.0
32.5°	221.5
35°	190.0
37.5°	159.0
40°	129.4
42.5°	101.8
45°	78.5
47.5°	57.7
50°	33.4
52.5°	14.5
55°	9.2
57.5°	8.7
60°	7.8
62.5°	7.3
65°	6.3
67.5°	5.8
70°	4.8
72.5°	4.4
75°	3.9
77.5°	2.9
80°	2.4
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)