

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269261

Luminaire Tested: P3AS05R709740DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709740DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 488.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269261

CATALOG NUMBER: P3AS05R709740DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1269261

CATALOG NUMBER: P3AS05R709740DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	82		89	85	81		86	83	80		84	81	79
4	94	86	80	75		93	85	79	75		83	78	74		81	76	73		79	75	72
5	89	80	73	69		87	79	73	68		77	72	68		75	71	67		74	70	66
6	84	74	68	63		82	73	67	63		72	66	62		70	65	62		69	65	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	53		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49
10	67	57	50	46		66	56	50	46		55	50	46		55	49	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94466
5°	93330
10°	90646
15°	86811
20°	81300
25°	73867
30°	63807
35°	50862
40°	37041
45°	24344
50°	11394
55°	3517
60°	3421
65°	3269
70°	3077
75°	3304
80°	3031
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24344 cd/sqm

TEST NUMBER: P1269261

CATALOG NUMBER: P3AS05R709740DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.9	8.2
10°-20°	107.0	21.9
20°-30°	139.1	28.5
30°-40°	118.0	24.2
40°-50°	60.9	12.5
50°-60°	11.7	2.4
60°-70°	6.4	1.3
70°-80°	3.9	0.8
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.0	58.6
0°-40°	404.1	82.8
0°-60°	476.6	97.7
0°-90°	488.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	431	
5°	424	40
15°	382	107
25°	305	139
35°	190	118
45°	78	61
55°	9	12
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1269261

CATALOG NUMBER: P3AS05R709740DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	430.8
2.5°	429.4
5°	424.0
7.5°	416.3
10°	407.1
12.5°	395.5
15°	382.4
17.5°	366.4
20°	348.4
22.5°	328.1
25°	305.3
27.5°	279.6
30°	252.0
32.5°	221.5
35°	190.0
37.5°	159.0
40°	129.4
42.5°	101.8
45°	78.5
47.5°	57.7
50°	33.4
52.5°	14.5
55°	9.2
57.5°	8.7
60°	7.8
62.5°	7.3
65°	6.3
67.5°	5.8
70°	4.8
72.5°	4.4
75°	3.9
77.5°	2.9
80°	2.4
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)